

Hexagon nut DIN 934 Steel Zinc plated yellow passivated |10| M20

Article number	04122.200.001
Brand	-
UBB	950355979135
UNSPSC	31161727
EAN	8715493851085
PKG. of 20	Full Box Only

Technical Parameters

Diameter	M20
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M20
m	16
P	2.5
s	30

Technical Drawing

