

Hexagon nut turned DIN 934 Steel Plain [6] turned M2,5

Article number	11000.025.001
Brand	-
UBB	950355339595
UNSPSC	31161727
EAN	8715492567154
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2.5
Class	[6]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Info	turned

Standards

NF	E25-401
DIN	934
NEN	1560

Technical Specification

d-D	M2.5
m	2
P	0.45
s	5

Technical Drawing

