

Hexagon head bolt DIN 931 Steel Plain 8.8 M4X55

Article number	01000.040.055
Brand	-
UBB	500644971474
UNSPSC	31161620
EAN	8717077046795
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	55 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1555
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): $L \leq 125\text{mm}$	14
d-D	M4
k	2.8
L (mm)	55
P	0.7
s	7

Technical Drawing

