

Hexagon head bolt DIN 931 Steel Plain 8.8 M5X45



Article number	01000.050.045
Brand	-
UBB	950351001637
UNSPSC	31161620
EAN	8715492006936
PKG. of 200	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M5
Length (L) (mm)	45

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	22
b (min.): $L \leq 125\text{mm}$	16
k	3.5
P	0.80
s	8

Technical Drawing

