

Hexagon head bolt DIN 931 Steel Plain 8.8 M5X50

Article number	01000.050.050
Brand	-
UBB	950351001710
UNSPSC	31161620
EAN	8715492006943
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
ISO	4014
NEN	1555
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	50
P	0.8
s	8

Technical Drawing

