

## Hexagon head bolt DIN 931 Steel Plain 8.8 M6X55

|                |               |
|----------------|---------------|
| Article number | 01000.060.055 |
| Brand          | -             |
| UBB            | 950351002544  |
| UNSPSC         | 31161620      |
| EAN            | 8715492007094 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M6            |
| Length            | 55 mm         |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Plain         |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| ISO  | 4014       |
| NEN  | 1555       |
| ASME | B18.2.3.1M |
| DIN  | 931        |
| NF   | E25-112    |

### Technical Specification

|                           |    |
|---------------------------|----|
| b (min.):<br>125mmL≤200mm | 24 |
| b (min.): L≤125mm         | 18 |
| d-D                       | M6 |
| k                         | 4  |
| L (mm)                    | 55 |
| P                         | 1  |
| s                         | 10 |

### Technical Drawing

