

Hexagon head bolt DIN 931 Steel Plain 8.8 M8X40

Article number	01000.080.040
Brand	-
UBB	950351003799
UNSPSC	31161620
EAN	8715492007377
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mm $L \leq 200$ mm	28
b (min.): $L \leq 125$ mm	22
d-D	M8
k	5.3
L (mm)	40
P	1.25
s	13

Technical Drawing

