

Hexagon head bolt DIN 931 Steel Plain 8.8 M10X110

Article number	01000.100.110
Brand	-
UBB	950351006503
UNSPSC	31161620
EAN	8715492007742
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	110
P	1.5
s	17

Technical Drawing

