

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X60



| | |
|----------------|---------------|
| Article number | 01000.120.060 |
| Brand | - |
| UBB | 950351007675 |
| UNSPSC | 31161620 |
| EAN | 8715492007964 |
| PKG. of 100 | Full Box Only |

Technical Parameters

| | |
|--------------------------|---------------|
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Plain |
| Thread | Metric thread |
| Wrench width (s) (mm) | 19 |
| Diameter (d-D) | M12 |
| Length (L) (mm) | 60 |

Standards

| | |
|------|------------|
| NF | E25-112 |
| ISO | 4014 |
| DIN | 931 |
| ASME | B18.2.3.1M |

Technical Specification

| | |
|---|------|
| b (min.): 125mm $L \leq 200\text{mm}$ | 36 |
| b (min.): $L > 200\text{mm}$ | 49 |
| b (min.): $L \leq 125\text{mm}$ | 30 |
| k | 7.5 |
| P | 1.75 |
| s | 19 |

Technical Drawing

