

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X90

Article number	01000.120.090
Brand	-
UBB	950351008178
UNSPSC	31161620
EAN	8715492008039
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	90
P	1.75
s	19

Technical Drawing

