

Hexagon head bolt DIN 931 Steel Plain 8.8 M12X130

Article number	01000.120.130
Brand	-
UBB	950351008582
UNSPSC	31161620
EAN	8715492008084
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
DIN	931
ASME	B18.2.3.1M
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	130
P	1.75
s	19

Technical Drawing

