

Hexagon head bolt DIN 931 Steel Plain 8.8 M14X75



Article number	01000.140.075
Brand	-
UBB	950351010133
UNSPSC	31161620
EAN	8715492008299
PKG. of 50	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Wrench width (s) (mm)	22
Diameter (d-D)	M14
Length (L) (mm)	75

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	40
b (min.): L>200mm	53
b (min.): L≤125mm	34
k	8.8
P	2
s	22

Technical Drawing

