

Hexagon head bolt ISO 4014 Steel Right Plain 8.8 M16X55



Article No.	01000.160.055
Brand	-
UBB	950351011388
UNSPSC	31161620
EAN	8715492008503
PKG. of 50	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M16
Length (L) (mm)	55

Standards

ASME	B18.2.3.1M
ISO	4014
NF	E25-112
NEN	1555
DIN	931

Technical Specification

s	24
b (min.): L≤125mm	38
k	10
b (min.): 125mm<L≤200mm	44
P	2
b (min.): L>200mm	57

Technical Drawing

