

Hexagon head bolt DIN 931 Steel Plain 8.8 M16X270



Article number	01000.160.270
Brand	-
UBB	952351313806
UNSPSC	31161620
EAN	8715492008756
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M16
Length (L) (mm)	270

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	44
b (min.): $L > 200\text{mm}$	57
b (min.): $L \leq 125\text{mm}$	38
k	10
P	2
s	24

Technical Drawing

