

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X85

Article number	01000.200.085
Brand	-
UBB	952351146594
UNSPSC	31161620
EAN	8715492009197
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	85 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	85
P	2.5
s	30

Technical Drawing

