

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X240

Article number	01000.200.240
Brand	-
UBB	950351016908
UNSPSC	31161620
EAN	8715492009388
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	240
P	2.5
s	30

Technical Drawing

