

Hexagon head bolt DIN 931 Steel Plain 8.8 M20X390

Article number	01000.200.390
Brand	-
UBB	500644577602
UNSPSC	31161620
EAN	8717077006317
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M20
Length	390 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	390
P	2.5
s	30

Technical Drawing

