

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X110

Article number	01000.240.110
Brand	-
UBB	950351903964
UNSPSC	31161620
EAN	8715492009845
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
DIN	931
NEN	1555
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	110
P	3
s	36

Technical Drawing

