

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X120

Article number	01000.240.120
Brand	-
UBB	950351020116
UNSPSC	31161620
EAN	8715492009852
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M24
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NEN	1555
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	60
b (min.): L200mm	73
b (min.): L≤125mm	54
d-D	M24
k	15
L (mm)	120
P	3
s	36

Technical Drawing

