

## Hexagon head bolt DIN 931 Steel Plain 8.8 M24X130



Article number	01000.240.130
Brand	-
UBB	950351020298
UNSPSC	31161620
EAN	8715492009869
PKG. of 10	Full Box Only

### Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M24
Length (L) (mm)	130

### Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	60
b (min.): $L > 200\text{mm}$	73
b (min.): $L \leq 125\text{mm}$	54
k	15
P	3
s	36

### Technical Drawing

