

Hexagon head bolt DIN 931 Steel Plain 8.8 M24X210



Article number	01000.240.210
Brand	-
UBB	950351915018
UNSPSC	31161620
EAN	8715492009944
PKG. of 10	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M24
Length (L) (mm)	210

Standards

ISO	4014
DIN	931
NF	E25-112
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	60
b (min.): $L > 200\text{mm}$	73
b (min.): $L \leq 125\text{mm}$	54
k	15
P	3
s	36

Technical Drawing

