

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X170

Article number	01000.270.170
Brand	-
UBB	950351022922
UNSPSC	31161620
EAN	8715492010254
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M27
Length	170 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ISO	4014
NEN	1555
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	170
P	3
s	41

Technical Drawing

