

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X340

Article number	01000.270.340
Brand	-
UBB	950351023912
UNSPSC	31161620
EAN	8715492010384
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M27
Length	340 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	340
P	3
s	41

Technical Drawing

