

Hexagon head bolt DIN 931 Steel Plain 8.8 M27X540

Article number	01000.270.540
Brand	-
UBB	500644581802
UNSPSC	31161620
EAN	8717077006737
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M27
Length	540 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	66
b (min.): L200mm	79
b (min.): L≤125mm	60
d-D	M27
k	17
L (mm)	540
P	3
s	41

Technical Drawing

