

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X190

Article number	01000.300.190
Brand	-
UBB	950351025321
UNSPSC	31161620
EAN	8715492010551
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M30
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	190
P	3.5
s	46

Technical Drawing

