

Hexagon head bolt DIN 931 Steel Plain 8.8 M30X330

Article number	01000.300.330
Brand	-
UBB	500644582552
UNSPSC	31161620
EAN	8717077006805
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M30
Length	330 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NEN	1555
ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	72
b (min.): L200mm	85
b (min.): L≤125mm	66
d-D	M30
k	18.7
L (mm)	330
P	3.5
s	46

Technical Drawing

