

Hexagon head bolt DIN 931 Steel Plain 8.8 M33X120

Article number	01000.330.120
Brand	-
UBB	950351026980
UNSPSC	31161620
EAN	8715492010797
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	120
P	3.5
s	50

Technical Drawing

