

Hexagon head bolt DIN 931 Steel Plain 8.8 M33X140

Article number	01000.330.140
Brand	-
UBB	950351027145
UNSPSC	31161620
EAN	8715492010810
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M33
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
ISO	4014
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	78
b (min.): L200mm	91
b (min.): L≤125mm	72
d-D	M33
k	21
L (mm)	140
P	3.5
s	50

Technical Drawing

