

Hexagon head bolt DIN 931 Steel Plain 8.8 M36X120

Article number	01000.360.120
Brand	-
UBB	950351028705
UNSPSC	31161620
EAN	8715492011060
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M36
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
NEN	1555
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	84
b (min.): L200mm	97
b (min.): L≤125mm	78
d-D	M36
k	22.5
L (mm)	120
P	4
s	55

Technical Drawing

