

Hexagon head bolt DIN 931 Steel Plain 8.8 M36X190



Article number	01000.360.190
Brand	-
UBB	950351029463
UNSPSC	31161620
EAN	8715492011138
PKG. of 2	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M36
Length (L) (mm)	190

Standards

ISO	4014
NF	E25-112
ASME	B18.2.3.1M
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	84
b (min.): $L > 200\text{mm}$	97
b (min.): $L \leq 125\text{mm}$	78
k	22.5
P	4
s	55

Technical Drawing

