


## Hexagon head bolt ISO 4014 Steel Right Plain 8.8 M42X340



Article No.	01000.420.340
Brand	-
UBB	952351209871
UNSPSC	31161620
EAN	8715492011763
PKG. of 1	Full Box Only

### Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M42
Length (L) (mm)	340

### Standards

NEN	1555
DIN	931
ASME	B18.2.3.1M
ISO	4014
NF	E25-112

### Technical Specification

k	26
P	4.50
b (min.): 125mm<L≤200mm	96
s	65
b (min.): L>200mm	109
b (min.): L≤125mm	90

### Technical Drawing

