

Hexagon head bolt DIN 931 Steel Plain 8.8 M52X180



Article number	01000.520.180
Brand	-
UBB	950351036054
UNSPSC	31161620
EAN	8715492012326
PKG. of 1	Full Box Only

Technical Parameters

Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread
Diameter (d-D)	M52
Length (L) (mm)	180

Standards

ASME	B18.2.3.1M
ISO	4014
DIN	931
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	116
b (min.): $L > 200\text{mm}$	119
k	33
P	5
s	80

Technical Drawing

