

Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 90 M5X14



Article number	01049.050.014
Brand	-
UBB	500577288540
UNSPSC	31161620
EAN	8715494322546
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	14
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

DIN ≈6921

Technical Specification

d_c	11.2
k	4.3
P	0.80
s	8

Technical Drawing

