



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 90 M5X16

Article number	01049.050.016
Brand	-
UBB	500577288623
UNSPSC	31161620
EAN	8715494322553
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	16 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M5
dc	11.2
k	4.3
L (mm)	16
P	0.8
s	8

Technical Drawing

