



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 90 M8X12

Article number	01049.080.012
Brand	-
UBB	500577289613
UNSPSC	31161620
EAN	8715494322652
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	12 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M8
dc	18.2
k	7
L (mm)	12
P	1.25
s	13

Technical Drawing

