



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 100 M16X35

Article number	01049.160.035
Brand	-
UBB	500577292419
UNSPSC	31161620
EAN	8715494327909
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	35 mm
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN ≈6921

Technical Specification

d-D	M16
dc	31
k	11.2
L (mm)	35
P	2
s	22

Technical Drawing

