



## Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc plated 100 M16X50

|                |               |
|----------------|---------------|
| Article number | 01049.160.050 |
| Brand          | -             |
| UBB            | 500577292740  |
| UNSPSC         | 31161620      |
| EAN            | 8715494327930 |
| PKG. of 50     | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M16           |
| Length            | 50 mm         |
| Class             | 100           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.

### Standards

DIN      ≈6921

### Technical Specification

|        |      |
|--------|------|
| d-D    | M16  |
| dc     | 31   |
| k      | 11.2 |
| L (mm) | 50   |
| P      | 2    |
| s      | 22   |

### Technical Drawing

