



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Plain 90 M5X12

Article number	01050.050.012
Brand	-
UBB	950351122599
UNSPSC	31161620
EAN	8715492018939
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M5
dc	11.2
k	4.3
L (mm)	12
P	0.8
s	8

Technical Drawing

