



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Plain 90 M6X10

Article number	01050.060.010
Brand	-
UBB	950351122839
UNSPSC	31161620
EAN	8715492018960
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	10 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info

Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M6
dc	14.2
k	5.5
L (mm)	10
P	1
s	10

Technical Drawing

