

Hexagon flange bolt with toothed flange DIN ≈6921 Steel Plain 100 M12X30



Article number	01050.120.030
Brand	-
UBB	950351124991
UNSPSC	31161620
EAN	8715492019202
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	30
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
 Warning:
 electroplating of
 these products may
 cause hydrogen
 embrittlement.

Standards

DIN ≈6921

Technical Specification

d_c	24
k	8.7
P	1.75
s	17

Technical Drawing

