



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Plain 100 M16X25

Article number	01050.160.025
Brand	-
UBB	950351125493
UNSPSC	31161620
EAN	8715492019332
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	25 mm
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Info
Warning:
electroplating of
these products may
cause hydrogen
embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M16
dc	31
k	11.2
L (mm)	25
P	2
s	22

Technical Drawing

