



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M5X10

Article number	01055.050.010
Brand	-
UBB	500644989542
UNSPSC	31161620
EAN	8717077048607
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	10 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M5
dc	11.2
k	4.3
L (mm)	10
P	0.8
s	8

Technical Drawing

