



## Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M6X10

|                |               |
|----------------|---------------|
| Article number | 01055.060.010 |
| Brand          | -             |
| UBB            | 500571174621  |
| UNSPSC         | 31161620      |
| EAN            | 8715494147316 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                   |                                                                              |
|-------------------|------------------------------------------------------------------------------|
| Diameter          | M6                                                                           |
| Length            | 10 mm                                                                        |
| Class             | 90                                                                           |
| Driving features  | Hexagon                                                                      |
| Head shape        | Hexagon head                                                                 |
| Material          | Steel                                                                        |
| Thread direction  | Right                                                                        |
| Surface treatment | Zinc flake Cr6+free -<br>ISO 10683 flZnnc                                    |
| Thread            | Metric thread                                                                |
| Info              | A zinc flake coating<br>eliminates the<br>risk of hydrogen<br>embrittlement. |

### Standards

|     |       |
|-----|-------|
| DIN | ≈6921 |
|-----|-------|

### Technical Specification

|        |      |
|--------|------|
| d-D    | M6   |
| dc     | 14.2 |
| k      | 5.5  |
| L (mm) | 10   |
| P      | 1    |
| s      | 10   |

### Technical Drawing

