



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M6X20

Article number	01055.060.020
Brand	-
UBB	500571174886
UNSPSC	31161620
EAN	8715494147347
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M6
Length	20 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M6
dc	14.2
k	5.5
L (mm)	20
P	1
s	10

Technical Drawing

