



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M8X12

Article number	01055.080.012
Brand	-
UBB	500571175040
UNSPSC	31161620
EAN	8715494147361
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	12 mm
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M8
dc	18.2
k	7
L (mm)	12
P	1.25
s	13

Technical Drawing

