

Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 90 M10X16



Article number	01055.100.016
Brand	-
UBB	500644989880
UNSPSC	31161620
EAN	8717077048638
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	16
Class	90
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - flZn/nc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d_c	21
k	7.9
P	1.50
s	15

Technical Drawing

