

Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 fIZnnc 100 M12X20



Article number	01055.120.020
Brand	-
UBB	500644990029
UNSPSC	31161620
EAN	8717077048652
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	20
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr(VI) free - fIZn/nc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d_c	24
k	8.7
P	1.75
s	17

Technical Drawing

