



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 100 M12X40

Article number	01055.120.040
Brand	-
UBB	500571175875
UNSPSC	31161620
EAN	8715494147453
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	40 mm
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M12
dc	24
k	8.7
L (mm)	40
P	1.75
s	17

Technical Drawing

