



Hexagon flange bolt with toothed flange DIN ≈6921 Steel Zinc flake Cr6+free - ISO 10683 flZnnc 100 M16X35

Article number	01055.160.035
Brand	-
UBB	500644990698
UNSPSC	31161620
EAN	8717077048713
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M16
Length	35 mm
Class	100
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc flake Cr6+free - ISO 10683 flZnnc
Thread	Metric thread
Info	A zinc flake coating eliminates the risk of hydrogen embrittlement.

Standards

DIN	≈6921
-----	-------

Technical Specification

d-D	M16
dc	31
k	11.2
L (mm)	35
P	2
s	22

Technical Drawing

