



Hexagon head bolt MF DIN 960 Steel Plain 8.8 M8X1,00X40

Article number	01060.080.040
Brand	-
UBB	950351126558
UNSPSC	31161620
EAN	8715492019516
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Standards

NEN	1555
NF	E25-152
ISO	8765
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L200mm	41
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	40
P	1
s	13

Technical Drawing

